


 Click [here](#) for the 3D model.

General Information

Style	Thin Flexible Actuator
Description	Piezoelectric Haptic Module
RoHS	Yes
REACH	Yes

Dimensions

L	18.5mm +/-0.2mm
W	14.1mm +/-0.2mm
T	0.6mm +/-0.1mm

Packaging Specifications

Packaging	Tray, Box
Packaging Quantity	180

Specifications

Series	FFAA
Maximum Driving Voltage	212 V Peak-Peak
Temperature Range	0/+60°C
Stimulus Signal Current	100 mA (Peak inrush current)
Frequency	500 Hz Max Voltage Frequency
Assembly Temperature	+100C
Max dV/dt	0.5 V/us

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.