


FMOV224ZF

Aliases (USCFM00V224Z00)

FM, Supercapacitors, Radial Molded, 0.22 F, -20/+80%, 3.5 VDC, Wire Leads, 5mm



Click [here](#) for the 3D model.

Dimensions

W	10.5mm +/-0.5mm
H	11.5mm +/-0.5mm
T	6.5mm +/-0.5mm
S	5mm +/-0.5mm
LL	5mm +/-1mm
G	0.4mm +/-0.1mm
LT1	0.5mm +/-0.1mm
LT2	0.4mm +/-0.1mm

Packaging Specifications

Lead	Wire Leads
Packaging	Bulk, Box
Packaging Quantity	1000

General Information

Series	FM
Style	Radial Molded
Description	Radial Molded Double Layer Capacitor
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Typical Component Weight	1.6 g
Miscellaneous	DischargeValue = 0.3 F.

Specifications

Capacitance	0.22 F
Capacitance Tolerance	-20/+80%
Voltage DC	3.5 VDC
Temperature Range	-25/+70°C
Rated Temperature	70°C
ESR	100000 mOhms (1kHz)
Discharge Current	0.2 mAmps (30 Minutes After Charging)