


[Click here for the 3D model.](#)
General Information

Series	FS
Style	Radial Pin
Description	Radial Cylindrical Double Layer Capacitor
RoHS	Yes
Lead	Pin Leads
AEC-Q200	No
Typical Component Weight	160 g
Miscellaneous	DischargeValue = 6.5 F.

Dimensions

D	44.8mm +/-0.5mm
H	60mm MAX
S	20mm +/-0.5mm
LL Negative	9.8mm MIN
LL Positive	9.5mm MIN
LT1	1mm +/-0.1mm
LT2	1.4mm +/-0.1mm

Specifications

Capacitance	5 F
Tolerance	-20/+80%
Voltage DC	12 VDC
Temperature Range	-25/+70°C
Rated Temperature	70°C
ESR	4000 mOhms (1kHz)
Current (at 30 minutes after charging)	18 mAmps

Packaging Specifications

Packaging	Bulk, Box
Packaging Quantity	20

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.