


GL-2030H2

Aliases (UNFGL2030H2XXX)

Obsolete

 ${\sf EMI \, Filters, \, KEMET, \, GL, \, Metal \, Box, \, Noise \, Suppression}$



General Information	
Series	GL
Style	Metal Box
Description	Noise Filters
RoHS	With Exemptions
Qualifications	TUV
AEC-Q200	No
Miscellaneous	30 K Self-Temperature Rise Max.
Lead	Screw Terminals
Terminal Type	Screw

Click here for the 3D model.

Dimensions	
L	81.5mm NOM
W	50mm NOM
Н	37mm NOM
Lead	Screw Terminals

Packaging Specifications	
Packaging	Tray, Box
Packaging Quantity	20
Typical Component Weight	90 q

Specifications	
Voltage AC	250 VAC
Voltage	1500 VAC Withstanding Voltage 1 Min. Line to Ground
Rated Current	3 A (AC/DC)
Ripple Current	3 A (AC/DC)
Rated Temperature	55°C
Temperature Range	-25/+55°C
Leakage Current	0.5 mA
ESR	300 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/28/2025 © 2006 - 2025 YAGEO