


[Click here for the 3D model.](#)
**General Information**

Series	FLLD3-PV
Style	Chassis Mount
Description	EMI Filter, Chassis Mount, With Y Capacitor
Features	Three Phase, High Performance, High Voltage
Phase	Three-phase
RoHS	Yes
Qualifications	IEC/EN 60939, UL 1283
Lead	Threaded Studs M10
Terminal Type	Threaded Studs M10

**Dimensions**

L	300mm NOM
W	180mm NOM
H	125mm NOM
L1	120mm NOM
W1	205mm NOM
W2	230mm NOM
U	55mm NOM
X	5mm NOM
Y	20mm NOM
Z	45mm NOM
I	15mm NOM
N	9mm NOM
M (Earth)	Threaded Studs M10
Lead	Threaded Studs M10

**Specifications**

Voltage AC	520 VAC
Rated Frequency	50-60 Hz
Rated Current	250 A (50°C)
Ripple Current	250 A (50°C)
Rated Temperature	50°C
Temperature Range	-40/+100°C
Climate Category	40/100/21
Test Voltage DC (P to P)	2250 VDC
Test Voltage DC (P to E)	3000 VDC
Max Power Loss	15 W (25°C 50 Hz)
Leakage Current	5 mA

**Packaging Specifications**

Packaging	Bulk
Packaging Quantity	1
Typical Component Weight	7,000 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.