


FLLD4016ATHT3

Aliases (LLD4016ATHT3)

KEMET, FLLD4-TH, EMI/RFI Filters, Noise Suppression, 530 VAC, 16 A, 120x115x80mm



Click [here](#) for the 3D model.

Dimensions

L	120mm NOM
W	115mm NOM
H	80mm NOM
L1	80mm NOM
W1	127.5mm NOM
W2	143mm NOM
J	32mm NOM
K	6.5mm NOM
M (Earth)	Threaded Studs M6

Packaging Specifications

Packaging	Bulk
Packaging Quantity	1
Typical Component Weight	800 g

General Information

Series	FLLD4-TH
Style	Chassis Mount
Description	EMI Filter, Chassis Mount, Compact
Features	High Performance
Phase	Three-phase + Neutral
RoHS	Yes
Qualifications	IEC/EN 60939
Terminal Type	Terminal Block

Specifications

Voltage AC	530 VAC
Rated Frequency	50-60 Hz
Rated Current	16 A (50°C)
Ripple Current	16 A (50°C)
Rated Temperature	50°C
Temperature Range	-25/+100°C
Climate Category	25/100/21
Test Voltage DC (P to P)	2250 VDC
Test Voltage DC (P to E)	3000 VDC
Power Loss	6 W (25°C 50 Hz)
Leakage Current	11 mA