


FLLD4025ATHT3

Aliases (LLD4025ATHT3)

Obsolete

EMI Filters, KEMET, FLLD4-TH, Chassis Mount, Noise Suppression, 130x125x115mm



General Information	
Series	FLLD4-TH
Style	Chassis Mount
Description	EMI Filter, Classis Mount, Compact
Features	High Performance
Phase	Three-phase + Neutral
RoHS	Yes
Qualifications	IEC/EN 60939
AEC-Q200	No
Terminal Type	Terminal Block

Click here for the 3D model.

Dimensions	
L	130mm NOM
W	125mm NOM
Н	115mm NOM
L1	90mm NOM
W1	137.5mm NOM
W2	153mm NOM
J	32mm NOM
K	6.5mm NOM
M (Earth)	Threaded Studs M6

Packaging Specifications	
Packaging	Bulk
Packaging Quantity	1
Typical Component Weight	1,200 g

Specifications	
Voltage AC	530 VAC
Rated Frequency	50-60 Hz
Rated Current	25 A (50°C)
Ripple Current	25 A (50°C)
Rated Temperature	50°C
Temperature Range	-25/+100°C
Climate Category	25/100/21
Test Voltage DC (P to P)	2250 VDC
Test Voltage DC (P to E)	3000 VDC
Max Power Loss	12 W (25°C 50 Hz)
Leakage Current	11 mA

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/08/2025 © 2006 - 2025 YAGEO