



Click [here](#) for the 3D model.

Dimensions	
W	10.5mm +/-0.5mm
H	11.5mm +/-0.5mm
T	5mm +/-0.5mm
S	5mm +/-0.5mm
LL	5mm +/-1mm
G	0.4mm +/-0.1mm
LT1	0.5mm +/-0.1mm
LT2	0.4mm +/-0.1mm

Packaging Specifications	
Lead	Wire Leads
Packaging	Bulk, Box
Packaging Quantity	1000

General Information	
Series	FM
Description	Radial Molded Double Layer Capacitor
RoHS	Yes
AEC-Q200	No
Typical Component Weight	1.3 g
Miscellaneous	DischargeValue = 0.06 F.

Specifications	
Capacitance	0.047 F
Capacitance Tolerance	-20/+80%
Voltage DC	5.5 VDC
Temperature Range	-25/+70°C
Rated Temperature	70°C
ESR	200000 mOhms (1kHz)
Discharge Current	0.071 mAmps (30 Minutes After Charging)