


JSNEJ5350KB6L0

Aliases (SNEJ5350KB6L0)

JSN, Film, Metallized Polyester Stacked, Automotive Grade, 35 uF, 10%, 100 VDC, 63 VAC, 105°C, 17.3X30X15.4, 15.4mm



Click [here](#) for the 3D model.

Dimensions

Chip Size 17.3X30X15.4

L 17.3mm MAX

W 30mm MAX

T 15.4mm MAX

LL 2mm +/-1mm

F 0.3mm +/-0.1mm

B 2mm +/-1mm

Packaging Specifications

Packaging Tray

Packaging Quantity 252

General Information

Series	JSN
Dielectric	Metallized Polyester Stacked
Style	SMD Chip
RoHS	Yes
Lead	J Leads
Qualifications	AEC-Q200
AEC-Q200	Yes
Typical Component Weight	4.008 g
Shelf Life	104 Weeks

Specifications

Capacitance	35 uF
Capacitance Tolerance	10%
Voltage DC	100 VDC
Voltage AC	63 VAC
Temperature Range	-55/+125°C
Rated Temperature	105°C
Dissipation Factor	1% 1kHz
Max dV/dt	27 V/us