


## L0603C2R2MDMIT

Aliases (L0603C2R2MDMIT)

Obsolete

KEMET, L-DMI, Ferrite, 20%, 2,200 nH



General Information	
Series	L-DMI
Style	SMD Multi-Layer
Core	Ferrite
Description	Shielded, Surface Mount Inductor
RoHS	Yes

Click here for the 3D model.

Dimensions	
L	1.6mm +/-0.15mm
W	0.8mm +/-0.15mm
Т	0.95mm MAX
Packaging Specifications	
Packaging	T&R
Packaging Quantity	4000

Specifications	
Inductance	2.2 uH (1 MHz)
Inductance Tolerance	20%
Rated Current	650 mAmps (MAX)
Temperature Range	-40/+85°C
Shielded	Yes
DC Resistance	300 mOhms
DC Resistance	0.3 Ohms (Max)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/30/2025 © 2006 - 2025 YAGEO