


## **L1210R101MDWIT**

Aliases (L1210R101MDWIT)

Obsolete

Scheduled EOL - Last date to buy 30 JUN 2023 KEMET, L-DWI, Ferrite, 20%, 100 uH, 1210



Click	here	for the	<sup>2</sup> 3D	model.
CIICK	nere	TOL LITE	= 20	model

General Information	
Series	L-DWI
Style	SMD Wire-Wound
Core	Ferrite
Description	Surface Mount Inductor
Features	High Current Type
RoHS	Yes
Notes	Last Order Date June 30, 2023. Suggested Replacement - https://productfinder.pulseelect ronics.com/part/BWNC 00372926101K00.

Dimensions				
Chip Size	1210			
L	3.2mm +/-0.2mm			
W	2.5mm +/-0.2mm			
Т	2.5mm +/-0.2mm			
Packaging Specifications				

T&R

1000

Packaging

Packaging Quantity

Specifications	
Inductance	100 uH (0.1 MHz)
Inductance Tolerance	20%
Rated Current	340 mAmps (Irms, 40C Rise By Self Heating)
Saturation Current	270 mAmps (Isat, 30% Drop In Inductance)
Temperature Range	-40/+105°C
DC Resistance	1.4 Ohms
DC Resistance	1.4 Ohms
Self-Resonant Frequency	6 MHz

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/29/2025 © 2006 - 2025 YAGEO