

## GT-20301

Aliases (UNFGT20301XXXX)

Obsolete

KEMET, GT, EMI/RFI Filters, Noise Suppression, 250 VAC

Click [here](#) for the 3D model.

Dimensions	
L	93mm NOM
W	53mm NOM
H	30mm NOM
L1	85mm NOM
L2	74.7mm NOM
Lead	Fast On

Packaging Specifications	
Packaging	Tray
Packaging Quantity	30
Typical Component Weight	160 g

General Information	
Series	GT
Style	Metal Box
Description	Noise Filters
RoHS	With Exemptions
SCIP Number	97462fd0-8e28-4245-8658-d38f8b19fa11
Qualifications	UL, CSA, TUV
Notes	Last time buy due: May 31, 2024.
Miscellaneous	30 K Self-Temperature Rise Max.
Lead	Fast On
Terminal Type	Faston

Specifications	
Voltage AC	250 VAC
Voltage	1500 VAC Withstanding Voltage 1 Min. Line to Ground
Rated Current	3 A (AC/DC)
Temperature Range	-25/+55°C
Leakage Current	1 mA MAX (250 V 60 Hz)
ESR	300 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.