


HHBC14-1R2A0067V

Aliases (UALC141R2A0067)

Differential Mode Chokes - Power, KEMET, HHBC, Through-Hole, Normal Mode, 67 uH, 20%



General Information	
Series	HHBC
Style	Through-Hole
Features	Noise Solution, Switching Power Supply Outlets, DC-DC Converter
RoHS	Yes
Miscellaneous	40 (K) Temperature Rise Max.
Core	Fe-Si

Dimensions	
D	33.5mm MAX
L	33.5mm MAX
Т	17.1mm MAX
LL	9mm +/-3mm
S	14mm NOM
Wire Size	1.2mm

	Specifications	
33.5mm MAX	Inductance	67 uH
33.5mm MAX	Inductance Tolerance	20%
17.1mm MAX	Rated Current	8 A
9mm +/-3mm	Temperature Range	-40/+125°C
14mm NOM	DC Resistance	22.2 mOhms
1.2mm		

Packaging Specifications		
Packaging	Tray	
Packaging Quantity	120	
Typical Component Weight	37 g	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/13/2025 © 2006 - 2025 YAGEO