


JSNDJ5680KB6L0

Aliases (SNDJ5680KB6L0)

JSN, Film, Metallized Polyester Stacked, Automotive Grade, 68 uF, 10%, 63 VDC, 40 VAC, 105°C, 17.3X30X15.7, 15.7mm



Click [here](#) for the 3D model.

Dimensions

Chip Size	17.3X30X15.7
L	17.3mm MAX
W	30mm MAX
T	15.7mm MAX
LL	2mm +/-1mm
F	0.3mm +/-0.1mm
B	2mm +/-1mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	252

General Information

Series	JSN
Dielectric	Metallized Polyester Stacked
Style	SMD Chip
RoHS	Yes
Lead	J Leads
Qualifications	AEC-Q200
AEC-Q200	Yes
Typical Component Weight	4.008 g
Shelf Life	104 Weeks

Specifications

Capacitance	68 uF
Capacitance Tolerance	10%
Voltage DC	63 VDC
Voltage AC	40 VAC
Temperature Range	-55/+125°C
Rated Temperature	105°C
Dissipation Factor	1% 1kHz
Max dV/dt	25 V/us