


LF-202-9

Aliases (UNFLF2029XXXXX)

Obsolete

EMI Filters, KEMET, LF, Metal Box, Noise Suppression



General Information	
Series	LF
Style	Metal Box
Description	Metal Box
Features	Small Current
Phase	Three-phase
RoHS	Yes
Miscellaneous	30 K Self-Temperature Rise Max.

Click here for the 3D model.

Dimensions	
L	48mm NOM
W	50mm NOM
Н	22mm NOM
Packaging Specifications	
Packaging	Tray, Box
Packaging Quantity	10
Typical Component Weight	50 g

Specifications	
Voltage AC	250 VAC
Rated Current	2 A (AC/DC)
Ripple Current	2 A (AC/DC)
Rated Temperature	55°C
Temperature Range	-25/+55°C
Leakage Current	0.005 mA
ESR	300 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/04/2025 © 2006 - 2025 YAGEO