


LF-220N

Aliases (UNFLF220NXXXXX)

Obsolete

KEMET, LF, EMI/RFI Filters, Noise Suppression, 250 VAC, 20 A



Click [here](#) for the 3D model.

Dimensions

L	160mm NOM
W	70mm NOM
H	60mm NOM
Lead	Screw Terminals

Packaging Specifications

Packaging	Tray, Box
Packaging Quantity	12
Typical Component Weight	1200 g

General Information

Series	LF
Style	Metal Box
Description	Metal Box
Phase	Three-phase
RoHS	With Exemptions
Miscellaneous	30 K Self-Temperature Rise Max.
Lead	Screw Terminals
Terminal Type	Screw

Specifications

Voltage AC	250 VAC
Rated Current	20 A (AC/DC)
Ripple Current	20 A (AC/DC)
Rated Temperature	55°C
Temperature Range	-20/+55°C
Leakage Current	1 mA MAX (250 V 60 Hz)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.