


## LF-240

Aliases (UNFLF240XXXXXX)

Obsolete

KEMET, LF, EMI/RFI Filters, Noise Suppression, 250 VAC



Click [here](#) for the 3D model.

### Dimensions

L	210mm NOM
W	120mm NOM
H	75mm NOM
S	60mm NOM
L1	190mm NOM
L2	170mm NOM
W1	100mm NOM
I	40mm NOM

### Packaging Specifications

Packaging	Tray, Box
Packaging Quantity	5
Typical Component Weight	3200 g

### General Information

Series	LF
Style	Metal Box
Description	Metal Box
Features	Large Current
Phase	Three-phase
RoHS	With Exemptions
SCIP Number	b0e85b87-59cd-457a-8d24-f3b2cc44e1fb
Notes	Last time buy due: May 31, 2024.
Miscellaneous	40 K Self-Temperature Rise Max.

### Specifications

Voltage AC	250 VAC
Voltage	1500 VAC Withstanding Voltage 1Min. Line to Ground
Rated Current	40 A (AC/DC)
Rated Temperature	45°C
Temperature Range	-20/+45°C
Leakage Current	1mA MAX (250 V 60 Hz)
ESR	300 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground