


## LF-250P

Aliases (UNFLF250PXXXXX)

Obsolete

KEMET, LF, EMI/RFI Filters, Noise Suppression, 250 VAC, 50 A



Click [here](#) for the 3D model.

### General Information

Series	LF
Style	Metal Box
Description	Metal Box
Features	Large Current
Phase	Three-phase
RoHS	With Exemptions
Miscellaneous	40 K Self-Temperature Rise Max.

### Specifications

Voltage AC	250 VAC
Rated Current	50 A (AC/DC)
Ripple Current	50 A (AC/DC)
Rated Temperature	45°C
Temperature Range	-20/+45°C
Leakage Current	1 mA MAX (250 V 60 Hz)

### Dimensions

L	240mm NOM
W	90mm NOM
H	80mm NOM
S	40mm NOM
L1	220mm NOM
W1	70mm NOM

### Packaging Specifications

Packaging	Tray, Box
Packaging Quantity	5
Typical Component Weight	4000 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.