


L1210R1R0MDWIT

Aliases (L1210R1R0MDWIT)
Obsolete

Scheduled EOL - Last date to buy 30 JUN 2023 KEMET, L-DWI, Ferrite, 20%, 1,000 nH



Click	here	for	the	3D	model	
CIICK	Hele	101	uie	$^{\circ}$	model	

General Information	
Series	L-DWI
Style	SMD Wire-Wound
Core	Ferrite
Description	Surface Mount Inductor
Features	High Current Type
RoHS	Yes
Notes	Last Order Date June 30, 2023. Suggested Replacement - https://productfinder.pulseelect ronics.com/part/BWNC 003729261R0K00.

Dimensions	
L	3.2mm +/-0.2mm
W	2.5mm +/-0.2mm
Т	2.5mm +/-0.2mm

Packaging Specifications	
Packaging	T&R
Packaging Quantity	1000

Specifications	
Inductance	1 uH (0.1 MHz)
Inductance Tolerance	20%
Rated Current	1440 mAmps (Irms, 40C Rise By Self Heating)
Saturation Current	2000 mAmps (Isat, 30% Drop In Inductance)
Temperature Range	-40/+105°C
DC Resistance	55 mOhms
DC Resistance	0.055 Ohms
Self-Resonant Frequency	250 MHz

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/14/2025 © 2006 - 2025 YAGEO