



Click [here](#) for the 3D model.

**General Information**

Series	LF
Style	Metal Box
Description	Metal Box
Features	Three-Phase
Phase	Three-phase
RoHS	With Exemptions
SCIP Number	b0e85b87-59cd-457a-8d24-f3 b2cc44e1fb
Miscellaneous	40 K Self-Temperature Rise Max.

**Dimensions**

L	180mm NOM
W	240mm NOM
H	80mm NOM
S	50mm NOM
L1	160mm NOM
W1	220mm NOM
W2	200mm NOM
U	30mm NOM
I	40mm NOM

**Specifications**

Voltage AC	250 VAC
Voltage	1500 VAC Withstanding Voltage 1 Min. Line to Ground
Rated Current	40 A (AC/DC)
Ripple Current	40 A (AC/DC)
Rated Temperature	45°C
Temperature Range	-20/+45°C
Leakage Current	1 mA
ESR	300 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground

**Packaging Specifications**

Packaging	Tray, Box
Packaging Quantity	3
Typical Component Weight	5300 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.