


L1210R680KDWT

Aliases (L1210R680KDWT)

Obsolete

Scheduled EOL - Last date to buy 30 JUN 2023

KEMET, L-DWI, Ferrite, 10%, 68 uH



Click [here](#) for the 3D model.

General Information

| | |
|-------------|--|
| Series | L-DWI |
| Style | SMD Wire-Wound |
| Core | Ferrite |
| Description | Surface Mount Inductor |
| Features | High Current Type |
| RoHS | Yes |
| Notes | Last Order Date June 30, 2023. Suggested Replacement - https://productfinder.pulseelectronics.com/part/BWNC00372926680K00 . |

Specifications

| | |
|-------------------------|--|
| Inductance | 68 uH (0.1 MHz) |
| Inductance Tolerance | 10% |
| Rated Current | 410 mAmps (Irms, 40C Rise By Self Heating) |
| Saturation Current | 320 mAmps (Isat, 30% Drop In Inductance) |
| Temperature Range | -40/+105°C |
| DC Resistance | 1 Ohms |
| DC Resistance | 1 Ohms |
| Self-Resonant Frequency | 8 MHz |

Dimensions

| | |
|---|----------------|
| L | 3.2mm +/-0.2mm |
| W | 2.5mm +/-0.2mm |
| T | 2.5mm +/-0.2mm |

Packaging Specifications

| | |
|--------------------|------|
| Packaging | T&R |
| Packaging Quantity | 1000 |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.