


MMC12.7684K100B31TR24

Aliases (F160YR684K100V, MMC100DB6680KB31T1)

Obsolete

MMC/F160, Film, Metallized Polyester, General Purpose, 0.68 uF, 10%, 100 VDC, 63 VAC, 100°C, 6.5 mm, 5045 / 127114



General Information	
Series	MMC/F160
Dielectric	Metallized Polyester
Style	SMD Chip
RoHS	Yes
AEC-Q200	No
Typical Component Weight	1.683 g
Miscellaneous	Not For New Design. Use F161YR684K100V (Series F161).
Shelf Life	104 Weeks

Note: '()' correspond to the letters used in the product bulletin

Click here for the 3D model.

Dimensions	
L	12.7mm +/-0.2mm
W	11.5mm +/-0.2mm
Т	6.5mm +/-0.2mm
F	0.5mm NOM
Case Code (EIA / mm)	5045 / 127114
Packaging Specifications	
Packaging	T&R
Packaging Quantity	600

Specifications	
Capacitance	0.68 uF
Tolerance	10%
Voltage DC	100 VDC
Voltage AC	63 VAC
Temperature Range	-55/+100°C
Rated Temperature	100°C
Dissipation Factor	0.8% 1kHz, 1.2% 10kHz, 3% 100kHz
Insulation Resistance	7.3529 GOhms
Max dV/dt	12 V/us

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/22/2025 © 2006 - 2025 YAGEO