



Click [here](#) for the 3D model.

#### General Information

|                          |                                                                                                                          |
|--------------------------|--------------------------------------------------------------------------------------------------------------------------|
| Series                   | MMK/F601                                                                                                                 |
| Dielectric               | Metallized Polyester                                                                                                     |
| Style                    | Radial                                                                                                                   |
| Features                 | DC Multipurpose Applications                                                                                             |
| RoHS                     | Yes                                                                                                                      |
| Termination              | Tinned Wire                                                                                                              |
| Lead                     | Wire Leads                                                                                                               |
| Typical Component Weight | 1.395 g                                                                                                                  |
| Notes                    | *Obsolete. Please check possible alternative parts in R82, RSB (pitch 5mm), R66 (pitch 7.5mm) and R60 (pitch 10-37.5mm). |

#### Dimensions

|    |              |
|----|--------------|
| L  | 7.2mm MAX    |
| H  | 13mm MAX     |
| T  | 7.2mm MAX    |
| S  | 5mm +/-0.4mm |
| LL | 5mm NOM      |
| F  | 0.5mm NOM    |

#### Packaging Specifications

|                    |           |
|--------------------|-----------|
| Packaging          | Bulk, Bag |
| Packaging Quantity | 1000      |

#### Specifications

|                       |                                  |
|-----------------------|----------------------------------|
| Capacitance           | 0.12 uF                          |
| Tolerance             | 5%                               |
| Voltage DC            | 400 VDC, 310 VDC (100C)          |
| Voltage AC            | 200 VAC                          |
| Temperature Range     | -55/+100°C                       |
| Rated Temperature     | 85°C                             |
| Dissipation Factor    | 0.8% 1kHz, 1.2% 10kHz, 3% 100kHz |
| Insulation Resistance | 30 GOhms                         |
| Max dV/dt             | 50 V/us                          |
| Inductance            | 6 nH                             |