


MMK7.5822J630K01L4BULK

Aliases (F601KG822J630C, MMK7.5822J630K01L4BULK)

Obsolete

Recommended Replacement Series R60

MMK/F601, Film, Metallized Polyester, General Purpose, 8,200 pF, 5%, 630 VDC, 85°C, 7.5 mm



Click [here](#) for the 3D model.

General Information

Series	MMK/F601
Dielectric	Metallized Polyester
Style	Radial
Features	DC Multipurpose Applications
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
Typical Component Weight	0.538 g
Notes	*Obsolete. Please check possible alternative parts in R82, RSB (pitch 5mm), R66 (pitch 7.5mm) and R60 (pitch 10-37.5mm).

Specifications

Capacitance	8,200 pF
Tolerance	5%
Voltage DC	630 VDC, 488.3 VDC (100C)
Voltage AC	220 VAC
Temperature Range	-55/+100°C
Rated Temperature	85°C
Dissipation Factor	0.8% 1kHz, 1.5% 10kHz, 3% 100kHz
Insulation Resistance	30 GOhms
Max dV/dt	60 V/us
Inductance	6 nH

Dimensions

L	10mm MAX
H	8mm MAX
T	4mm MAX
S	7.5mm +/-0.4mm
LL	5mm NOM
F	0.6mm NOM

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	1000

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.