



Click [here](#) for the 3D model.

Dimensions

Chip Size	4340
AEC-Q200	Yes
L	10.8mm +/-0.3mm
W	10mm +/-0.2mm
T	4mm MAX
G	3mm +/-0.3mm

Packaging Specifications

Typical Component Weight	2.2 g
Packaging	T&R, 330mm
Packaging Quantity	500

General Information

Series	MPEV
Style	SMD Molded
Core	Metal Composite
Description	Surface Mount Inductor
Features	Power Inductors
RoHS	Yes
Qualifications	AEC-Q200
AEC-Q200	Yes
Miscellaneous	40 (K) Temperature Rise Max.

Specifications

Inductance	2200 nH
Inductance Tolerance	20%
Temperature Range	-55/+180°C
Shielded	Yes
Current	14.6 A (Irms, 40C Rise By Self Heating), 13 A (Isat, 20% Drop In Inductance), 18.5 A (Isat, 30% Drop In Inductance)
DC Resistance	7.9 mOhms
Self-Resonant Frequency	23 MHz