


MPX1D0618L4R7

Aliases (UPI2X10618L4R7)

KEMET, MPX, Metal Composite, 20%, 4700 nH, 0618(2826)



Click [here](#) for the 3D model.

Dimensions

Chip Size	0618(2826)
L	7mm +/-0.25mm
W	6.5mm +/-0.2mm
T	1.8mm MAX
G	3.2mm +/-0.3mm

Packaging Specifications

Typical Component Weight	370 mg
Packaging	T&R, 330mm
Packaging Quantity	2500

General Information

Series	MPX
Style	SMD Molded
Core	Metal Composite
Description	Surface Mount Inductor
Features	Power Inductors
RoHS	Yes
Miscellaneous	40 (K) Temperature Rise Max.

Specifications

Inductance	4700 nH
Inductance Tolerance	20%
Temperature Range	-55/+155°C
Shielded	Yes
Current	3.4 A (I _{rms} , 40C Rise By Self Heating), 4 A (I _{sat} , 20% Drop In Inductance), 6 A (I _{sat} , 30% Drop In Inductance)
DC Resistance	83.4 mOhms
Self-Resonant Frequency	26 MHz

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.