


MPCH1040L1R0

Aliases (UPIC1040L1R000)

KEMET, MPCH, Metal Composite, 20%, 1000 nH, 1040(4340)



Click [here](#) for the 3D model.

Dimensions

Chip Size	1040(4340)
L	11.5mm MAX
W	10mm +/-0.3mm
T	4mm MAX
G	3mm +/-0.5mm

Packaging Specifications

Typical Component Weight	2.3 g
Packaging	T&R, 330mm
Packaging Quantity	1000

General Information

Series	MPCH
Style	SMD Molded
Core	Metal Composite
Description	Shielded, Surface Mount Inductor
Features	Large Current Inductors
RoHS	Yes
Miscellaneous	40 (K) Temperature Rise Max.

Specifications

Inductance	1000 nH
Inductance Tolerance	20%
Temperature Range	-40/+125°C
Rated Temperature	120°C
Shielded	true
Current	17 A (Isat, 20% Drop In Inductance), 17 A (Irms, 40C Rise By Self Heating)
DC Resistance	2.3 mOhms