



Click [here](#) for the 3D model.

Dimensions

Chip Size	0624(2826)
L	7mm +/-0.25mm
W	6.5mm +/-0.2mm
T	2.4mm MAX
G	3.2mm +/-0.3mm

Packaging Specifications

Typical Component Weight	500 mg
Packaging	T&R, 330mm
Packaging Quantity	1500

General Information

Series	MPX
Style	SMD Molded
Core	Metal Composite
Description	Surface Mount Inductor
Features	Power Inductors
RoHS	Yes
Miscellaneous	40 (K) Temperature Rise Max.

Specifications

Inductance	220 nH
Inductance Tolerance	20%
Temperature Range	-55/+155°C
Shielded	true
Current	19.4 A (Irms, 40C Rise By Self Heating), 19.5 A (Isat, 20% Drop In Inductance), 29 A (Isat, 30% Drop In Inductance)
DC Resistance	3.3 mOhms
Self-Resonant Frequency	120 MHz