



Click [here](#) for the 3D model.

#### Dimensions

Chip Size	0830(3431)
L	8.65mm +/-0.25mm
W	8mm +/-0.2mm
T	3mm MAX
G	5.1mm +/-0.3mm

#### Packaging Specifications

Typical Component Weight	1.07 g
Packaging	T&R, 330mm
Packaging Quantity	1500

#### General Information

Series	MPX
Style	SMD Molded
Core	Metal Composite
Description	Surface Mount Inductor
Features	Power Inductors
RoHS	Yes
Miscellaneous	40 (K) Temperature Rise Max.

#### Specifications

Inductance	10 uH
Inductance Tolerance	20%
Temperature Range	-55/+155°C
Shielded	true
Current	5.4 A (Irms, 40C Rise By Self Heating), 5.5 A (Isat, 20% Drop In Inductance), 8 A (Isat, 30% Drop In Inductance)
DC Resistance	61.7 mOhms
Self-Resonant Frequency	12 MHz