


## MPX1D1040L330

Aliases (UPI2X11040L330)

KEMET, MPX, Metal Composite, 20%, 33 uH, 1040(4340)



Click [here](#) for the 3D model.

### Dimensions

Chip Size	1040(4340)
L	10.8mm +/-0.3mm
W	10mm +/-0.2mm
T	4mm MAX
G	3mm +/-0.3mm

### Packaging Specifications

Typical Component Weight	2.2 g
Packaging	T&R, 330mm
Packaging Quantity	500

### General Information

Series	MPX
Style	SMD Molded
Core	Metal Composite
Description	Surface Mount Inductor
Features	Power Inductors
RoHS	Yes
Miscellaneous	40 (K) Temperature Rise Max.

### Specifications

Inductance	33 uH
Inductance Tolerance	20%
Temperature Range	-55/+155°C
Shielded	Yes
Current	3.7 A (Irms, 40C Rise By Self Heating), 3.5 A (Isat, 20% Drop In Inductance), 5 A (Isat, 30% Drop In Inductance)
DC Resistance	119.7 mOhms
Self-Resonant Frequency	5 MHz