



Click [here](#) for the 3D model.

### Dimensions

Chip Size	1040(4340)
L	10.8mm +/-0.3mm
W	10mm +/-0.2mm
T	4mm MAX
G	4.7mm +/-0.3mm

### Packaging Specifications

Typical Component Weight	2.2 g
Packaging	T&R, 330mm
Packaging Quantity	500

### General Information

Series	MPX
Style	SMD Molded
Core	Metal Composite
Description	Surface Mount Inductor
Features	Power Inductors
RoHS	Yes
Miscellaneous	40 (K) Temperature Rise Max.

### Specifications

Inductance	330 nH
Inductance Tolerance	20%
Temperature Range	-55/+155°C
Shielded	Yes
Current	29.7 A (I <sub>rms</sub> , 40C Rise By Self Heating), 31 A (I <sub>sat</sub> , 20% Drop In Inductance), 47 A (I <sub>sat</sub> , 30% Drop In Inductance)
DC Resistance	1.9 mOhms
Self-Resonant Frequency	75 MHz