


MPX1D0520LR15

Aliases (UPI2X10520LR15)

KEMET, MPX, Metal Composite, 20%, 150 nH, 0520(2120)



Click [here](#) for the 3D model.

Dimensions

Chip Size	0520(2120)
L	5.3mm +/-0.2mm
W	5mm +/-0.2mm
T	2mm MAX
G	2.5mm +/-0.2mm

Packaging Specifications

Typical Component Weight	230 mg
Packaging	T&R, 330mm
Packaging Quantity	3500

General Information

Series	MPX
Style	SMD Molded
Core	Metal Composite
Description	Surface Mount Inductor
Features	Power Inductors
RoHS	Yes
Miscellaneous	40 (K) Temperature Rise Max.

Specifications

Inductance	150 nH
Inductance Tolerance	20%
Temperature Range	-55/+155°C
Shielded	Yes
Current	16.9 A (Irms, 40C Rise By Self Heating), 15.5 A (Isat, 20% Drop In Inductance), 22 A (Isat, 30% Drop In Inductance)
DC Resistance	3.9 mOhms
Self-Resonant Frequency	190 MHz

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.