



Click [here](#) for the 3D model.

Dimensions

| | |
|-----------|----------------|
| Chip Size | 0630(2826) |
| L | 7mm +/-0.25mm |
| W | 6.5mm +/-0.2mm |
| T | 3mm MAX |
| G | 3.2mm +/-0.3mm |

Packaging Specifications

| | |
|--------------------------|------------|
| Typical Component Weight | 620 mg |
| Packaging | T&R, 330mm |
| Packaging Quantity | 1500 |

General Information

| | |
|---------------|------------------------------|
| Series | MPX |
| Style | SMD Molded |
| Core | Metal Composite |
| Description | Surface Mount Inductor |
| Features | Power Inductors |
| RoHS | Yes |
| Miscellaneous | 40 (K) Temperature Rise Max. |

Specifications

| | |
|-------------------------|--|
| Inductance | 15 uH |
| Inductance Tolerance | 20% |
| Temperature Range | -55/+155°C |
| Shielded | true |
| Current | 3.3 A (Irms, 40C Rise By Self Heating), 3 A (Isat, 20% Drop In Inductance), 4 A (Isat, 30% Drop In Inductance) |
| DC Resistance | 130.2 mOhms |
| Self-Resonant Frequency | 13 MHz |