



Click [here](#) for the 3D model.

Dimensions

| | |
|-----------|----------------|
| Chip Size | 0530(2120) |
| AEC-Q200 | Yes |
| L | 5.3mm +/-0.2mm |
| W | 5mm +/-0.2mm |
| T | 3mm MAX |
| G | 2.5mm +/-0.2mm |

Packaging Specifications

| | |
|--------------------------|------------|
| Typical Component Weight | 330 mg |
| Packaging | T&R, 330mm |
| Packaging Quantity | 2500 |

General Information

| | |
|----------------|------------------------------|
| Series | MPXV |
| Style | SMD Molded |
| Core | Metal Composite |
| Description | Surface Mount Inductor |
| Features | Power Inductors |
| RoHS | Yes |
| Qualifications | AEC-Q200 |
| AEC-Q200 | Yes |
| Miscellaneous | 40 (K) Temperature Rise Max. |

Specifications

| | |
|-------------------------|--|
| Inductance | 4700 nH |
| Inductance Tolerance | 20% |
| Temperature Range | -55/+155°C |
| Shielded | true |
| Current | 4.6 A (Irms, 40C Rise By Self Heating), 3 A (Isat, 20% Drop In Inductance), 4.5 A (Isat, 30% Drop In Inductance) |
| DC Resistance | 62.2 mOhms |
| Self-Resonant Frequency | 26 MHz |