



Click [here](#) for the 3D model.

Dimensions

Chip Size	1250(5350)
L	13.2mm +/-0.4mm
W	12.5mm +/-0.2mm
T	5mm MAX
G	4.7mm +/-0.3mm

Packaging Specifications

Typical Component Weight	4.2 g
Packaging	T&R, 330mm
Packaging Quantity	250

General Information

Series	MPX
Style	SMD Molded
Core	Metal Composite
Description	Surface Mount Inductor
Features	Power Inductors
RoHS	Yes
Miscellaneous	40 (K) Temperature Rise Max.

Specifications

Inductance	10 uH
Inductance Tolerance	20%
Temperature Range	-55/+155°C
Shielded	Yes
Current	10.1 A (I _{rms} , 40C Rise By Self Heating), 9 A (I _{sat} , 20% Drop In Inductance), 13.5 A (I _{sat} , 30% Drop In Inductance)
DC Resistance	20.6 mOhms
Self-Resonant Frequency	8.5 MHz