



Click [here](#) for the 3D model.

#### Dimensions

|           |                 |
|-----------|-----------------|
| Chip Size | 1250(5350)      |
| L         | 13.2mm +/-0.4mm |
| W         | 12.5mm +/-0.2mm |
| T         | 5mm MAX         |
| G         | 4.7mm +/-0.3mm  |

#### Packaging Specifications

|                          |            |
|--------------------------|------------|
| Typical Component Weight | 4.2 g      |
| Packaging                | T&R, 330mm |
| Packaging Quantity       | 250        |

#### General Information

|               |                              |
|---------------|------------------------------|
| Series        | MPX                          |
| Style         | SMD Molded                   |
| Core          | Metal Composite              |
| Description   | Surface Mount Inductor       |
| Features      | Power Inductors              |
| RoHS          | Yes                          |
| Miscellaneous | 40 (K) Temperature Rise Max. |

#### Specifications

|                         |   |
|-------------------------|---|
| Inductance              | 330 nH  |
| Inductance Tolerance    | 20%   |
| Temperature Range       | -55/+155°C  |
| Shielded                | true  |
| Current                 | 41.6 A (Irms, 40C Rise By Self Heating), 45 A (Isat, 20% Drop In Inductance), 65 A (Isat, 30% Drop In Inductance) |
| DC Resistance           | 1.3 mOhms   |
| Self-Resonant Frequency | 68 MHz  |