



Click [here](#) for the 3D model.

Dimensions

Chip Size	1740(6868)
L	17mm +/-0.5mm
W	17.1mm +/-0.5mm
T	4mm MAX
G	11.9mm NOM

Packaging Specifications

Typical Component Weight	6.3 g
Packaging	T&R, 330mm
Packaging Quantity	100

General Information

Series	MPX
Style	SMD Molded
Core	Metal Composite
Description	Surface Mount Inductor
Features	Power Inductors
RoHS	Yes
Miscellaneous	40 (K) Temperature Rise Max.

Specifications

Inductance	1500 nH
Inductance Tolerance	20%
Temperature Range	-55/+155°C
Shielded	true
Current	23.5 A (Irms, 40C Rise By Self Heating), 19.5 A (Isat, 20% Drop In Inductance), 28 A (Isat, 30% Drop In Inductance)
DC Resistance	3.8 mOhms
Self-Resonant Frequency	24 MHz