



Click [here](#) for the 3D model.

Dimensions

Chip Size	1040(4340)
AEC-Q200	Yes
L	10.8mm +/-0.3mm
W	10mm +/-0.2mm
T	4mm MAX
G	4.7mm +/-0.3mm

Packaging Specifications

Typical Component Weight	2.2 g
Packaging	T&R, 330mm
Packaging Quantity	500

General Information

Series	MPXV
Style	SMD Molded
Core	Metal Composite
Description	Surface Mount Inductor
Features	Power Inductors
RoHS	Yes
Qualifications	AEC-Q200
AEC-Q200	Yes
Miscellaneous	40 (K) Temperature Rise Max.

Specifications

Inductance	470 nH
Inductance Tolerance	20%
Temperature Range	-55/+155°C
Shielded	true
Current	26.4 A (I _{rms} , 40C Rise By Self Heating), 29 A (I _{sat} , 20% Drop In Inductance), 42 A (I _{sat} , 30% Drop In Inductance)
DC Resistance	2.4 mOhms
Self-Resonant Frequency	65 MHz