



Click [here](#) for the 3D model.

Dimensions

Chip Size	0530(2120)
AEC-Q200	Yes
L	5.3mm +/-0.2mm
W	5mm +/-0.2mm
T	3mm MAX
G	2.5mm +/-0.2mm

Packaging Specifications

Typical Component Weight	330 mg
Packaging	T&R, 330mm
Packaging Quantity	2500

General Information

Series	MPXV
Style	SMD Molded
Core	Metal Composite
Description	Surface Mount Inductor
Features	Power Inductors
RoHS	Yes
Qualifications	AEC-Q200
AEC-Q200	Yes
Miscellaneous	40 (K) Temperature Rise Max.

Specifications

Inductance	6800 nH
Inductance Tolerance	20%
Temperature Range	-55/+155°C
Shielded	Yes
Current	3.5 A (Irms, 40C Rise By Self Heating), 2.5 A (Isat, 20% Drop In Inductance), 4 A (Isat, 30% Drop In Inductance)
DC Resistance	107.8 mOhms
Self-Resonant Frequency	23 MHz