


**General Information**

|                |                                 |
|----------------|---------------------------------|
| Series         | MR                              |
| Style          | Plastic Box                     |
| Description    | Noise Filters                   |
| RoHS           | With Exemptions                 |
| Qualifications | UL, CSA                         |
| Miscellaneous  | 30 K Self-Temperature Rise Max. |
| Lead           | Fast On                         |
| Terminal Type  | Faston                          |

[Click here for the 3D model.](#)
**Dimensions**

|      |          |                   |                                                     |
|------|----------|-------------------|-----------------------------------------------------|
| L    | 49mm NOM | Voltage AC        | 250 VAC                                             |
| W    | 40mm NOM | Voltage           | 1500 VAC Withstanding Voltage 1 Min. Line to Ground |
| H    | 27mm NOM | Rated Current     | 3 A (AC/DC)                                         |
| Lead | Fast On  | Ripple Current    | 3 A (AC/DC)                                         |
|      |          | Temperature Range | -20/+60°C                                           |

**Packaging Specifications**

|                          |           |     |                                                        |
|--------------------------|-----------|-----|--------------------------------------------------------|
| Packaging                | Tray, Box | ESR | 300 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground |
| Packaging Quantity       | 100       |     |                                                        |
| Typical Component Weight | 35 g      |     |                                                        |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.