



Click [here](#) for the 3D model.

Dimensions

D	11mm MIN
H	10.5mm MAX
D2	28mm MAX
D3	30.5mm MAX
D4	6mm NOM
LL	67mm +/-3mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	300
Typical Component Weight	11.9 g

General Information

Series	MR
Type	Current
Style	Round - Toroidal
Description	Zero-Phase Current Transformers
Features	High Sensitivity, Compact
Lead	Cables
RoHS	Yes
REACH	Yes
Notes	Measurement Conditions: f=60Hz, R=300 Ohms, I _o =22.5 mAmps

Specifications

Temperature Range	-20/+80°C
Voltage DC	8 mV MIN (Output)
Current	60 Amps
ESR	30 Ohms
Miscellaneous	Overinput characteristics (After DC5A input) = 10% MAX.