


MR-4

Aliases (USEZ4000000000)

KEMET, MR, Current, Round - Toroidal, Zero Phase, High Sensitivity, Compact



Click [here](#) for the 3D model.

Dimensions

D	16.5mm MIN
H	10.8mm MAX
D2	32mm MAX
D3	34.5mm MAX
D4	7mm NOM
LL	67mm +/-3mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	300
Typical Component Weight	16.5 g

General Information

Series	MR
Type	Current
Style	Round - Toroidal
Description	Zero-Phase Current Transformers
Features	High Sensitivity, Compact
Lead	Cables
RoHS	Yes
REACH	Yes
Notes	Measurement Conditions: f=60Hz, R=300 Ohms, I _o =22.5 mAmps

Specifications

Temperature Range	-20/+80°C
Voltage DC	8 mV MIN (Output)
Current	125 Amps
ESR	30 Ohms
Miscellaneous	Overinput characteristics (After DC5A input) = 10% MAX.