


MPXV1D0830L1R5

Aliases (UPI2X10830V1R5)

KEMET, MPXV, Metal Composite, 20%, 1500 nH, 0830(3431)



Click [here](#) for the 3D model.

Dimensions

Chip Size	0830(3431)
AEC-Q200	Yes
L	8.65mm +/-0.25mm
W	8mm +/-0.2mm
T	3mm MAX
G	5.1mm +/-0.3mm

Packaging Specifications

Typical Component Weight	1.07 g
Packaging	T&R, 330mm
Packaging Quantity	1500

General Information

Series	MPXV
Style	SMD Molded
Core	Metal Composite
Description	Surface Mount Inductor
Features	Power Inductors
RoHS	Yes
Qualifications	AEC-Q200
AEC-Q200	Yes
Miscellaneous	40 (K) Temperature Rise Max.

Specifications

Inductance	1500 nH
Inductance Tolerance	20%
Temperature Range	-55/+155°C
Shielded	Yes
Current	14 A (Irms, 40C Rise By Self Heating), 13 A (Isat, 20% Drop In Inductance), 18 A (Isat, 30% Drop In Inductance)
DC Resistance	9.1 mOhms
Self-Resonant Frequency	37 MHz