



Click [here](#) for the 3D model.

Dimensions

Chip Size	1235(5350)
AEC-Q200	Yes
L	13.2mm +/-0.4mm
W	12.5mm +/-0.2mm
T	3.5mm MAX
G	3mm +/-0.3mm

Packaging Specifications

Typical Component Weight	2.9 g
Packaging	T&R, 330mm
Packaging Quantity	500

General Information

Series	MPXV
Style	SMD Molded
Core	Metal Composite
Description	Surface Mount Inductor
Features	Power Inductors
RoHS	Yes
Qualifications	AEC-Q200
AEC-Q200	Yes
Miscellaneous	40 (K) Temperature Rise Max.

Specifications

Inductance	680 nH
Inductance Tolerance	20%
Temperature Range	-55/+155°C
Shielded	true
Current	25.9 A (Irms, 40C Rise By Self Heating), 28 A (Isat, 20% Drop In Inductance), 40 A (Isat, 30% Drop In Inductance)
DC Resistance	2.9 mOhms
Self-Resonant Frequency	46 MHz