



Click [here](#) for the 3D model.

#### Dimensions

Chip Size	1250(5350)
AEC-Q200	Yes
L	13.2mm +/-0.4mm
W	12.5mm +/-0.2mm
T	5mm MAX
G	4.7mm +/-0.3mm

#### Packaging Specifications

Typical Component Weight	4.2 g
Packaging	T&R, 330mm
Packaging Quantity	250

#### General Information

Series	MPXV
Style	SMD Molded
Core	Metal Composite
Description	Surface Mount Inductor
Features	Power Inductors
RoHS	Yes
Qualifications	AEC-Q200
AEC-Q200	Yes
Miscellaneous	40 (K) Temperature Rise Max.

#### Specifications

Inductance	15 uH
Inductance Tolerance	20%
Temperature Range	-55/+155°C
Shielded	true
Current	8.2 A (Irms, 40C Rise By Self Heating), 7.5 A (Isat, 20% Drop In Inductance), 11 A (Isat, 30% Drop In Inductance)
DC Resistance	30.8 mOhms
Self-Resonant Frequency	7 MHz