



Click [here](#) for the 3D model.

#### Dimensions

Chip Size	1264(5350)
AEC-Q200	Yes
L	13.2mm +/-0.4mm
W	12.5mm +/-0.2mm
T	6.4mm MAX
G	4.7mm +/-0.3mm

#### Packaging Specifications

Typical Component Weight	5.5 g
Packaging	T&R, 330mm
Packaging Quantity	250

#### General Information

Series	MPXV
Style	SMD Molded
Core	Metal Composite
Description	Surface Mount Inductor
Features	Power Inductors
RoHS	Yes
Qualifications	AEC-Q200
AEC-Q200	Yes
Miscellaneous	40 (K) Temperature Rise Max.

#### Specifications

Inductance	330 nH
Inductance Tolerance	20%
Temperature Range	-55/+155°C
Shielded	true
Current	45.6 A (Irms, 40C Rise By Self Heating), 48 A (Isat, 20% Drop In Inductance), 70 A (Isat, 30% Drop In Inductance)
DC Resistance	1.2 mOhms
Self-Resonant Frequency	61 MHz