



Click [here](#) for the 3D model.

Dimensions

Chip Size	2213(9088)
AEC-Q200	Yes
L	22mm +/-0.5mm
W	22mm +/-0.5mm
T	13mm MAX
G	18.5mm NOM

Packaging Specifications

Typical Component Weight	37 g
Packaging	T&R, 330mm
Packaging Quantity	50

General Information

Series	MPXV
Style	SMD Molded
Core	Metal Composite
Description	Surface Mount Inductor
Features	Power Inductors
RoHS	Yes
Qualifications	AEC-Q200
AEC-Q200	Yes
Miscellaneous	40 (K) Temperature Rise Max.

Specifications

Inductance	22 uH
Inductance Tolerance	20%
Temperature Range	-55/+155°C
Shielded	true
Current	19.5 A (Irms, 40C Rise By Self Heating), 15 A (Isat, 20% Drop In Inductance), 20.5 A (Isat, 30% Drop In Inductance)
DC Resistance	13.2 mOhms
Self-Resonant Frequency	3.7 MHz