



Click [here](#) for the 3D model.

Dimensions	
L	18.5mm MAX
H	12.5mm MAX
T	6mm MAX
S	15.2mm +/-0.4mm
LL	30mm +5mm
F	0.8mm NOM

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	400

General Information	
Series	PME271M/P276
Dielectric	Metallized Paper
Style	Radial
Features	EMI Safety
RoHS	Yes
Lead	Wire Leads
Safety Class	X2
Qualifications	ENEC, UL, cUL
AEC-Q200	No
Construction	Molded
Typical Component Weight	2.7 g
Miscellaneous	SRF= 8.4 MHz.

Specifications	
Capacitance	0.033 uF
Capacitance Tolerance	20%
Voltage DC	630 VDC
Voltage AC	275 VAC (X2)
Temperature Range	-40/+110°C
Rated Temperature	110°C
Dissipation Factor	1.3% 1kHz
Insulation Resistance	12 GOhms
Max dV/dt	1200 V/us