


## PME271M568MR30

Aliases (P276QP683M275A)

PME271M/P276, Film, Metallized Paper, Safety, 0.068 uF, 20%, 275 VAC (X2), 630 VDC, 110°C, 15.2mm



Click [here](#) for the 3D model.

Dimensions	
L	18.5mm MAX
H	13.5mm MAX
T	7.8mm MAX
S	15.2mm +/-0.4mm
LL	30mm +5mm
F	0.8mm NOM

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	400

General Information	
Series	PME271M/P276
Dielectric	Metallized Paper
Style	Radial
Features	EMI Safety
RoHS	Yes
Lead	Wire Leads
Safety Class	X2
Qualifications	ENEC, UL, cUL
AEC-Q200	No
THB Performance	No
Construction	Molded
Typical Component Weight	2.97 g
Miscellaneous	SRF= 5.6 MHz.

Specifications	
Capacitance	0.068 uF
Capacitance Tolerance	20%
Voltage AC	275 VAC (X2)
Voltage DC	630 VDC
Temperature Range	-40/+110°C
Rated Temperature	110°C
Dissipation Factor	1.3% 1kHz
Insulation Resistance	12 GOhms
Max dV/dt	1200 V/us