


## SMP255FB5680MC31TR24

Aliases (P106ZS683M310V) SMP255, Film, Metallized Paper, Automotive Safety, 0.068 uF, 20%, 630 VDC, 310 VAC, 125°C, 7 mm



| General Information |                  |
|---------------------|------------------|
| Series              | SMP255           |
| Dielectric          | Metallized Paper |
| Style               | SMD Chip         |
| RoHS                | Yes              |
| Termination         | Tin              |
| Safety Class        | X2               |
| AEC-Q200            | Yes              |

Note: '()' correspond to the letters used in the product bulletin

**Dimensions** 

Packaging Quantity

| L                        | 16.5mm +0.4mm               |
|--------------------------|-----------------------------|
| W                        | 15mm +0.6mm                 |
| Т                        | 7mm +0.4mm                  |
| F                        | 0.5mm NOM                   |
|                          |                             |
| Packaging Specifications |                             |
| Packaging                | T&R, Horizontal Orientation |
|                          |                             |

500

| Specifications        |            |
|-----------------------|------------|
| Capacitance           | 0.068 uF   |
| Tolerance             | 20%        |
| Voltage DC            | 630 VDC    |
| Voltage AC            | 310 VAC    |
| Temperature Range     | -40/+125°C |
| Rated Temperature     | 125°C      |
| Dissipation Factor    | 1.3% 1kHz  |
| Insulation Resistance | 12 GOhms   |
| Max dV/dt             | 600 V/us   |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/05/2025 © 2006 - 2025 YAGEO